



Gripping force tester GFT-X

Superior Clamping and Gripping



GFT - X



- Id-No. 0890013
- 4150,00 EUR / piece
- available ex stock

Gripping force tester GFT-X



Gripping force tester GFT-X



Gripping force tester GFT-X

Characteristics

- Using of measuring heads of old GFT-generation is possible
- Terminal device is protected with a rubber cover against hits
- Analysis of data on PC via USB
- Operating instructions self-explanatory
- Easy teaching of measuring heads
- Suitable for O. D. clamping (additional measuring head)
- Absolutely wireless
- Operating range of measuring-head-handheld unit approx. 3 m (if the connection breaks down, the connection will be restored automatically)
- 6-jaw function is not possible

Gripping force tester GFT-X

GFT-X Chuck Explorer Software (inclusive):

- Analysis of measured values in kN and lbf
- Analysis of RPM-diagrams
- Presetting of enormous parameters (jaw type, description of chuck,...)
- Data transmission via EXCEL (also diagrams)




Gripping force tester GFT-X

Improvements:

	GFT	GFT-X
Interface	RS 232	USB 2.0
Max. clamping force / jaw	90 kN	90 kN
Max. RPM	6.000 min ⁻¹	6.000 min ⁻¹
Clamping diameter	72-108 mm	72-108 mm
Terminal device	With cable 220 V	With battery, wireless
Recharger	-	USB recharger
Display	Monochrome	Color screen
Measuring head duration	Approx. 1h	Approx. 1h

Superior Clamping and Gripping



J. Lehmann

Jens Lehmann, German goalkeeper legend,
brand ambassador of SCHUNK,
the family-owned company since 2012



www.schunk.com