


Superior Clamping and Gripping




Clamping concept KSM2


KSM2 clamping vice with grounded jaws



KSM2 clamping vice with grounded jaws




Fixed jaw, 40mm
Schunk-ID: 0490728




Adjustable jaw 40mm with
Parallel chuck jaw 40mm




Fixed jaw, 65mm
Schunk-ID: 0490729




Adjustable jaw 65mm with
Parallel chuck jaw 40mm




Adjustable jaw 65mm with
Parallel chuck jaw 65mm




Adjustable jaw 65mm with
Parallel chuck jaw 90mm




Fixed jaw, 90mm
Schunk-ID: 0490730




Adjustable jaw 90mm with
Parallel chuck jaw 40mm




Adjustable jaw 90mm with
Parallel chuck jaw 65mm




Adjustable jaw 90mm with
Parallel chuck jaw 90mm



KSM2 clamping vice with high-grip parallel chuck jaw



KSM2 clamping vice with high-grip parallel chuck jaw




Fixed jaw, 40mm
Schunk-ID: 0490728




Adjustable jaw 40mm with high-grip parallel chuck jaw 40mm




Fixed jaw, 65mm
Schunk-ID: 0490729




Adjustable jaw 65mm with high-grip parallel chuck jaw 40mm




Adjustable jaw 65mm with high-grip parallel chuck jaw 65mm




Adjustable jaw 65mm with high-grip parallel chuck jaw 90mm




Fixed jaw, 90mm
Schunk-ID: 0490730




Adjustable jaw 90mm with high-grip parallel chuck jaw 40mm




Adjustable jaw 90mm with high-grip parallel chuck jaw 65mm



Adjustable jaw 90mm with high-grip parallel chuck jaw 90mm




KSM2 clamping vice with high-grip pull-down jaw and high-grip pendulum jaw



KSM2 clamping vice with high-grip pull-down jaw and high-grip pendulum jaw

Fixed jaw, 40mm
Schunk-ID: 0490728




Adjustable jaw 40mm with high-grip pull-down jaw 40mm




Adjustable jaw 40mm with high-grip pendulum jaw 90mm




Fixed jaw, 65mm
Schunk-ID: 0490729




Adjustable jaw 65mm with high-grip pull-down jaw 40mm




Adjustable jaw 65mm with high-grip pendulum jaw 90mm






Fixed jaw, 90mm
Schunk-ID: 0490730




Adjustable jaw 90mm with high-grip pull-down jaw 40mm



Adjustable jaw 40mm with high-grip pendulum jaw 90mm




KSM2 clamping vice with high-grip wedge clamping element




KSM2 clamping vice with high-grip wedge clamping element



Fixed jaw, 40mm
Schunk-ID: 0490728




Fixed jaw, 65mm
Schunk-ID: 0490729




Fixed jaw, 90mm
Schunk-ID: 0490730



Wedge clamping element
with high-grip clamping face
Schunk-ID: 0490736




KSM2 clamping vice with smooth wedge clamping element




KSM2 clamping vice with smooth wedge clamping element



Fixed jaw, 40mm
Schunk-ID: 0490728



Fixed jaw, 65mm
Schunk-ID: 0490729



Fixed jaw, 90mm
Schunk-ID: 0490730



Wedge clamping element
with smooth clamping face
Schunk-ID: 0490735

