

certificate  
no. **HM 220154**  
dated 2022-09-05

Translation In any case, the German original shall prevail.

## DGUV Test Certificate

Name and address of the holder of the certificate: (customer) Schunk GmbH & Co. KG  
Spann- und Greiftechnik  
Bahnhofstr. 106-134  
74348 Lauffen/Neckar  
GERMANY

Product designation: **The gripper is suitable for collaborative operation, ensured by safe current limitation.**

Type: Co-act EGP-C- 25  
Co-act EGP-C- 40  
Co-act EGP-C- 50  
Co-act EGP-C- 64

Testing based on: GS-HM-20:2022-03 Industrial robot

Test report: 2022-0031 dated 24.08.2022

Further details: In the application the biomechanical limit values shall be in accordance with ISO TS 15066.

Follow-up certificate of MF 18007 dated 18.05.2018.

The type tested meets the requirements specified in article 3 para. 1 of the German Product Safety Act. Thus, the type tested also complies with the provisions laid down in the directive 2006/42/EC (**Machinery**). The holder of the certificate is entitled to affix the DGUV Test mark shown overleaf to the products complying with the type tested.

The present certificate including the right to affix the DGUV Test mark is valid until: **2027-09-04**

Further provisions concerning the validity, the extension of the validity and other conditions are laid down in the Rules of Procedure for Testing and Certification.

  
Dipl.-Ing. Jan Stegmann  
Head of Certification Body



## DGUV Test mark

---

