


ePlan – iTENDO² easy connect



Bezeichnung	Richtung	Spannung	V_min	V_max	I_min	I_max
Digital IN / 0-5; on; set	Eingang, digital	24V ± 20%	19.2 V	28.8 V	6 mA	-
Analog OUT / 0-10 V	Ausgang, analog	0-10 V	0 V	10 V	-	10 mA
Vin / 24 V	Eingang, Versorgung	24V ± 20%	19.2 V	28.8 V	-	500 mA
Digital OUT / 0-5	Ausgang, digital	24V ± 10%	21.6 V	26.4 V	-	20 mA pro Ausgang

Digital OUT	Funktion	Einschaltdauer
0	Sensor connected	-
1	Battery Alarm (< 20%)	> 5 sec
2	Machine has control	-
3*	Alarm limit	> 5 sec
4*	Trend upper limit	> 5 sec
5*	Trend lower limit	> 5 sec

* nur relevant für easy monitor Variante