


ePlan – iTENDO² easy connect



Description	Direction	Voltage	V_min	V_max	I_min	I_max
Digital IN / 0-5; on; set	Input, digital	24 V ±20%	19.2 V	28.8 V	6 mA	-
Analog OUT/ 0-10 V	Output, analog	0-10 V	0 V	10 V	-	10 mA
Vin/24 V	Input, power supply	24 V ±20%	19.2 V	28.8 V	-	500 mA
Digital OUT / 0-5	Output, digital	24 V ±10%	21.6 V	26.4 V	-	20 mA per output

Digital OUT	Function	On time
0	Sensor connected	-
1	Battery alarm (< 20%)	> 5 sec
2	Machine has control	-
3*	Alarm limit	> 5 sec
4*	Trend upper limit	> 5 sec
5*	Trend lower limit	> 5 sec

* Only relevant for easy monitor variant