



### SECTION 1: Identification

#### 1.1. Identification

Product form : Mixture  
Product name : LINOMAX plus

#### 1.2. Recommended use and restrictions on use

Recommended use : Lubricants, Greases and Release Products

#### 1.3. Supplier

##### Supplier

H.-D. SCHUNK GmbH & Co. Spanntechnik KG  
Lothringer Str. 23  
Mengen, 88512  
Germany  
T +49-7572-7614-1300  
[CMM@de.schunk.com](mailto:CMM@de.schunk.com)

##### Importer

SCHUNK Intec Inc., Werk  
211 Kitty Hawk Drive  
Morrisville, NC, 27560  
USA  
T +1-919-572-2705  
[info@us.schunk.com](mailto:info@us.schunk.com)

E-mail address of competent person responsible for the SDS: [sds@gbk-ingelheim.de](mailto:sds@gbk-ingelheim.de)

#### 1.4. Emergency telephone number

Emergency number : IN CASE OF EMERGENCY CALL INFOTRAC UNITED STATES: 1-800-535-5053 OR  
INTERNATIONAL +1-352-323-3500

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS US classification

Not classified

#### 2.2. GHS Label elements, including precautionary statements

##### GHS US labeling

No labeling applicable

#### 2.3. Other hazards which do not result in classification

No additional information available

#### 2.4. Unknown acute toxicity (GHS US)

No additional information available

### SECTION 3: Composition/Information on ingredients

#### 3.1. Substances

Not applicable

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### 3.2. Mixtures

Name	Product identifier	%	GHS US classification
Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy paraffinic	CAS-No.: 64742-54-7	20 - 30	Asp. Tox. 1, H304
Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy naphthenic	CAS-No.: 64742-52-5	10 - 20	Asp. Tox. 1, H304

Full text of hazard classes and H-statements : see section 16

## SECTION 4: First-aid measures

### 4.1. Description of first aid measures

- First-aid measures general : Move the affected person away from the contaminated area.
- First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing. If you feel unwell, seek medical advice.
- First-aid measures after skin contact : Remove/Take off immediately all contaminated clothing. Rinse and then wash skin thoroughly with water and soap. If skin irritation occurs: Get medical advice/attention.
- First-aid measures after eye contact : Wash with plenty of water (during 20 minutes minimum) with eyes wide open after taking off soft contact lenses and immediately take medical advice.
- First-aid measures after ingestion : Rinse mouth. Do not induce vomiting. Call a doctor.

### 4.2. Most important symptoms and effects (acute and delayed)

No additional information available

### 4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

## SECTION 5: Fire-fighting measures

### 5.1. Suitable (and unsuitable) extinguishing media

- Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide (CO<sub>2</sub>).
- Unsuitable extinguishing media : Do not use a solid water stream as it may scatter and spread fire.

### 5.2. Specific hazards arising from the chemical

Hazardous decomposition products in case of fire : Metal oxides. Carbon monoxide. Carbon dioxide. Nitrogen oxides. Phosphorus oxides.

### 5.3. Special protective equipment and precautions for fire-fighters

- Firefighting instructions : Do not allow run-off from fire fighting to enter drains or water courses.
- Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : Evacuate the danger area. Keep public away from danger area. Avoid dust formation. Respirator must be worn if exposed to dust.

#### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area.

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if product enters sewers or public waters.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Mechanically recover the product.  
Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13. Refer to protective measures listed in Sections 7 and 8.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Additional hazards when processed : Avoid formation of dust. Dust may form flammable and explosive mixture with air.  
Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product. Keep away from food, drink and animal feeding stuffs.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in original container. Keep container closed when not in use. Store in a well-ventilated place. Keep cool.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

No additional information available

### 8.2. Appropriate engineering controls

Appropriate engineering controls : Ensure good ventilation of the work station.  
Environmental exposure controls : Avoid release to the environment.

### 8.3. Individual protection measures/Personal protective equipment

#### Hand protection:

Choosing the proper glove is a decision that depends not only on the type of material, but also on other quality features, which differ for each manufacturer

Type	Material	Permeation	Thickness (mm)	Penetration
Chemically resistant protective gloves	Nitrile rubber, Fluoroelastomer (FKM)		0,4	

#### Eye protection:

Safety glasses

#### Skin and body protection:

Wear suitable protective clothing

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### Respiratory protection:

No respiratory protection needed under normal use conditions

Device	Filter type	Condition
Breathing equipment	Filter P (white)	Vapors, Aerosols

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Solid
Appearance	: Paste.
Color	: Beige
Odor	: slight odour
Odor threshold	: No data available
pH	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: No data available
Flash point	: 174 °C (Closed cup)
Relative evaporation rate (butyl acetate=1)	: No data available
Flammability (solid, gas)	: Non flammable.
Vapor pressure	: No data available
Relative vapor density at 20°C	: No data available
Relative density	: 1.32
Solubility	: No data available
Log Pow	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity, kinematic	: Not applicable
Viscosity, dynamic	: No data available
Explosion limits	: Not applicable
Explosive properties	: No data available
Oxidizing properties	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### 10.5. Incompatible materials

Oxidizing agent.

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified (Based on available data, the classification criteria are not met)  
Acute toxicity (dermal) : Not classified (Based on available data, the classification criteria are not met)  
Acute toxicity (inhalation) : Not classified (Based on available data, the classification criteria are not met)

#### Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)

LD50 oral rat	> 5000 mg/kg body weight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)
---------------	---

#### Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy paraffinic (64742-54-7)

LD50 oral rat	> 5000 mg/kg body weight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)
---------------	---

Skin corrosion/irritation : Not classified (Based on available data, the classification criteria are not met)  
Serious eye damage/irritation : Not classified (Based on available data, the classification criteria are not met)  
Respiratory or skin sensitization : Not classified (Based on available data, the classification criteria are not met)  
Germ cell mutagenicity : Not classified (Based on available data, the classification criteria are not met)  
Carcinogenicity : Not classified (Based on available data, the classification criteria are not met)  
Reproductive toxicity : Not classified (Based on available data, the classification criteria are not met)  
STOT-single exposure : Not classified (Based on available data, the classification criteria are not met)  
STOT-repeated exposure : Not classified (Based on available data, the classification criteria are not met)

#### Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy naphthenic (64742-52-5)

LOAEL (oral, rat, 90 days)	125 mg/kg body weight Animal: rat, Animal sex: male, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents)
----------------------------	--

NOAEC (inhalation, rat, dust/mist/fume, 90 days)	> 0.98 mg/l air Animal: rat, Guideline: OECD Guideline 412 (Subacute Inhalation Toxicity: 28-Day Study)
--	---

#### Baseoil - unspecified, Distillates (petroleum), hydrotreated heavy paraffinic (64742-54-7)

LOAEL (oral, rat, 90 days)	125 mg/kg body weight Animal: rat, Animal sex: male, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents)
----------------------------	--

NOAEC (inhalation, rat, dust/mist/fume, 90 days)	> 0.98 mg/l air Animal: rat, Guideline: OECD Guideline 412 (Subacute Inhalation Toxicity: 28-Day Study)
--	---

Aspiration hazard : Not classified (Based on available data, the classification criteria are not met)  
Viscosity, kinematic : No data available

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms or to cause long-term adverse effects in the environment.

### 12.2. Persistence and degradability

No additional information available

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### 12.3. Bioaccumulative potential

No additional information available

### 12.4. Mobility in soil

No additional information available

### 12.5. Other adverse effects

No additional information available

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

## SECTION 14: Transport information

In accordance with DOT / IMDG / IATA

DOT	IMDG	IATA
<b>14.1. UN number</b>		
Not regulated for transport		
<b>14.2. Proper Shipping Name</b>		
Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>		
Not regulated	Not regulated	Not regulated
<b>14.4. Packing group</b>		
Not regulated	Not regulated	Not regulated
<b>14.5. Environmental hazards</b>		
Not regulated	Not regulated	Not regulated
No supplementary information available		

### 14.6. Special precautions for user

#### DOT

Not regulated

#### IMDG

Not regulated

#### IATA

Not regulated

### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

### SECTION 15: Regulatory information

#### 15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

#### 15.2. International regulations

No additional information available

#### 15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

### SECTION 16: Other information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Other information

: Data of sections 4 to 8, as well as 10 to 12, do partly not refer to the use and the regular employing of the product (in this sense consult information on use and on product), but to liberation of major amounts in case of accidents and irregularities. The information describes exclusively the safety requirements for the product(s) and is based on the present level of our knowledge. The delivery specifications are contained in the corresponding product sheet. This data does not constitute a guarantee for the characteristics of the product(s) as defined by the legal warranty regulations.

Full text of H-phrases	
H304	May be fatal if swallowed and enters airways

Abbreviations and acronyms	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
BCF	Bioconcentration factor
ATE	Acute Toxicity Estimate
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
DOT	Department of Transport
TDG	Transportation of Dangerous Goods
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
GHS	Globally Harmonized System of Classification, Labelling and Packaging of Chemicals
IARC	International Agency for Research on Cancer
vPvB	Very Persistent and Very Bioaccumulative

# LINOMAX plus

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations  
SDS No: 00248-0004\_US

<b>Abbreviations and acronyms</b>	
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
IBC-Code	International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
MARPOL 73/78	MARPOL 73/78: International Convention for the Prevention of Pollution From Ships
ADG	Transport of Australian Dangerous Goods
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
ED	Endocrine disruptor

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should therefore not be construed as guaranteeing any specific property of the product.